



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

Plug Valves, Halliburton Lo Torc style

Service	Part Description	Part Number
STD	VALVE, .38" x 2"1502 STD 15M	VA0022
STD	VALVE, .38" x 2"1502 STD 15M (VITON)	VA0022V
STD	VALVE, 1" x 1" 13/16 10M	VA0029
STD	VALVE, 1" x 1" 13/16 15M	VA0028
STD	VALVE, 1" x 1" 13/16 20M STUDxFLG STD (ACT PATTERN)	VA0685
STD	VALVE, 1" x 1"1502 STD 15M	VA0218
STD	VALVE, 1" x 1"1502 STD 15M (ACTUATED)	VA0694
STD	VALVE, 1" x 1"1502 STD 15M (AIR ACTUATED-DOUBLE ACT)	VA0564
STD	VALVE, 1" x 1.5"1502 STD 15M	VA0375
STD	VALVE, 1" x 1.5"1502 STD 15M (ACTUATED)	VA0670
STD	VALVE, 1" x 1.5"1502 STD 15M (AIR ACTUATED-DOUBLE ACT)	VA0579
STD	VALVE, 1" x 1.5"1502 STD 15M *ACT PATT	VA0375-OA0160
STD	VALVE, 1" x 1.5"LPMM STD 10M	VA0429
STD	VALVE, 1" x 2 1/16 10M STD	VA0013
STD	VALVE, 1" x 2 1/16 10M STD (ACTUATED)	VA0626
STD	VALVE, 1" x 2 1/16 10M STD wACT PATTERN	VA0648
STD	VALVE, 1" x 2 1/16 15M STD	VA0014
STD	VALVE, 1" x 2 1/16 15M STD *ACT PATTERN	VA0014-OA0159
STD	VALVE, 1" x 2 1/16 15M STD (ACTUATED)	VA0733
STD	VALVE, 1" x 2 1/16 5M STD	VA0147
STD	VALVE, 1" x 2 1/16 5M STD (ACTUATED)	VA0438
STD	VALVE, 1" x 2 1/16 5M STD *ACT PATT	VA0147-OA0159
STD	VALVE, 1" x 2"1002 STD 10M	VA0555
STD	VALVE, 1" x 2"1502 STD 15M	VA0023
STD	VALVE, 1" x 2"1502 STD 15M (ACTUATED) BRC002	VA0398
STD	VALVE, 1" x 2"1502 STD 15M (ACTUATED) BRC012	VA0591
STD	VALVE, 1" x 2"1502 STD 15M (AIR ACTUATED)w/LOCKING PIN	VA0362
STD	VALVE, 1" x 2"1502 STD 15M (AIR ACTUATED-DOUBLE ACT)	VA0428
STD	VALVE, 1" x 2"1502 STD 15M (SS PLUG)	VA0023S
STD	VALVE, 1" x 2"1502 STD 15M (SS PLUG)(ACTUATED)	VA0379
STD	VALVE, 1" x 2"1502 STD 15M (VITON)	VA0023V
STD	VALVE, 1" x 2"1502 STD 15M *ACT PATT (AIR)	VA0534
STD	VALVE, 1" x 2"602 STD 6M	VA0760
STD	VALVE, 1" x 2"LPMM STD 10M	VA0015
STD	VALVE, 1" x 2"LPMM STD 10M (ACTUATED)	VA0593
STD	VALVE, 1" x 2"LPMM STD 10M *ACT PATTERN	VA0015-OA0160
STD	VALVE, 1" x 2"LPMM STD 10M w/1"LPF	VA0331
STD	VALVE, 1" x 2"LPMM STD 10M w/1"LPF (ACTUATED)	VA0553
STD	VALVE, 1" x 2"LPMM STD 5M	VA0025
STD	VALVE, 1" x B20 STD 15M	VA0259
STD	VALVE, 1"-1 13/16 15M x 2"1502F STD 15M	VA0296



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

STD	VALVE, 1"-1.5"1502F x 1"LPF STD 10M	VA0442
STD	VALVE, 1"-2 1/16 5M x 2"1502F STD	VA0167
STD	VALVE, 1"-2 1/16 5M x 2"602F STD	VA0200
STD	VALVE, 1"-2 1/16 5M x 2"602F STD (ACTUATED BRC002)	VA0485
STD	VALVE, 1.3" x 1 13/16 10M STD	VA0037
STD	VALVE, 1.3" x 2"1502 STD 15M	VA0031
STD	VALVE, 1.75" x 1 13/16 10M STD	VA0061
STD	VALVE, 1.75" x 1 13/16 15M STD (GEAR OP)	VA0723
STD	VALVE, 1.75" x 1 13/16 15M STD (HI-TEMP)	VA0351
STD	VALVE, 1.75" x 2 1/16 10M STD	VA0060
STD	VALVE, 1.75" x 2 1/16 15M STD	VA0059
STD	VALVE, 1.75" x 2 1/16 15M STD (NO TAPER) (ACTUATED)	VA0493
STD	VALVE, 1.75" x 2 1/16 15M STD (NO TAPER) (GEAR OP)	VA0494
STD	VALVE, 1.75" x 2 1/16 15M STD (NO TAPER) *ACT PATTERN	VA0496
STD	VALVE, 1.75" x 2 1/16 15M STD (NO TAPER) *ACT PATTERN	VA0495
STD	VALVE, 1.75" x 2"1502 STD 15M	VA0063
STD	VALVE, 1.75" x 2"1502 STD 15M (ACTUATED)	VA0578
STD	VALVE, 1.75"-2 1/16 10M x 2"1502F STD	VA0676
STD	VALVE, 2" x 1 13/16 10M STD	VA0146
STD	VALVE, 2" x 2 1/16 10M STD	VA0035
STD	VALVE, 2" x 2 1/16 10M STD (ACTUATED)	VA0734
STD	VALVE, 2" x 2 1/16 10M STD (GEAR OP)	VA0761
STD	VALVE, 2" x 2 1/16 10M STD (VITON)	VA0035V
STD	VALVE, 2" x 2 1/16 10M STD *ACT PATTERN	VA0035-OA0113
STD	VALVE, 2" x 2 1/16 15M STD	VA0033
STD	VALVE, 2" x 2 1/16 15M STD (ACTUATED)	VA0652
STD	VALVE, 2" x 2 1/16 15M STD (GEAR OP)	VA0708
STD	VALVE, 2" x 2 1/16 15M STD *ACT PATTERN	VA0662
STD	VALVE, 2" x 2 1/16 5M STD	VA0043
STD	VALVE, 2" x 2 1/16 5M STD (ACTUATED)	VA0731
STD	VALVE, 2" x 2"1002 STD 10M	VA0554
STD	VALVE, 2" x 2"1502 STD 10M (AIR ACTUATED)	VA0446
STD	VALVE, 2" x 2"1502 STD 15M	VA0006
STD	VALVE, 2" x 2"1502 STD 15M (ACTUATED) *BRC012	VA0339
STD	VALVE, 2" x 2"1502 STD 15M (ACTUATED) *BRC022	VA0458
STD	VALVE, 2" x 2"1502 STD 15M (ACTUATED)(VITON) *BRC022	VA0458V
STD	VALVE, 2" x 2"1502 STD 15M (AIR ACT'D)	VA0655
STD	VALVE, 2" x 2"1502 STD 15M (AIR ACT'D-FS)	VA0510
STD	VALVE, 2" x 2"1502 STD 15M (AIR ACT'D-FS) (HIGH-TEMP)	VA0764
STD	VALVE, 2" x 2"1502 STD 15M (AIR ACT'D-FS)w/LOCKING PIN	VA0490
STD	VALVE, 2" x 2"1502 STD 15M (GEAR OP)	VA0411
STD	VALVE, 2" x 2"1502 STD 15M (HI-TEMP)	VA0343
STD	VALVE, 2" x 2"1502 STD 15M (LOW TEMP)(AIR ACT'D-FS)	VA0705
STD	VALVE, 2" x 2"1502 STD 15M (VITON)	VA0006V
STD	VALVE, 2" x 2"1502 STD 15M (VITON) *ACT PATTERN	VA0006V-OA0113
STD	VALVE, 2" x 2"1502 STD 15M *ACT PATTERN	VA0006-OA0162
STD	VALVE, 2" x 2"602 STD 6M	VA0190
STD	VALVE, 2" x 2"LPFF STD 10M	VA0032



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

STD	VALVE, 2" x 2"LPFF STD 10M (HI-TEMP)	VA0348
STD	VALVE, 2" x 2"LPFF STD 10M (SS PLUG)	VA0032S
STD	VALVE, 2" x 2.38EU FF STD 10M	VA0040
STD	VALVE, 2" x 2.88EU FF STD 10M	VA0370
STD	VALVE, 2" x 3"1502 STD 15M	VA0363
STD	VALVE, 2" x 3"1502 STD 15M (GEAR OP)	VA0740
STD	VALVE, 2" x B20 STD 15M	VA0041
STD	VALVE, 2" x B20 STD 15M (HI-TEMP/CO2)	VA0487
STD	VALVE, 2" x B20 STD 15M (HI-TEMP/CO2) *ACT PATTERN	VA0487-OA0162
STD	VALVE, 2" x B20 STD 15M (HI-TEMP/CO2) GREASEAL	VA0712
STD	VALVE, 2" x WS20TN STD 15M (HI-TEMP)	VA0381
STD	VALVE, 2" x WS20TN STD 15M (HI-TEMP) (AIR ACTUATED)	VA0769
STD	VALVE, 2" x WS20TN STD 15M (HI-TEMP) *ACT	VA0381-OA0162
STD	VALVE, 2" x WS20TN STD 15M (HI-TEMP) *ACT PATTERN	VA0489
STD	VALVE, 2" x WS20TN STD 15M (HI-TEMP)(ACTUATED)*UNInsert	VA0514
STD	VALVE, 2"-2 1/16 10M x 2"1502F STD	VA0349
STD	VALVE, 2"-2 1/16 15M x 2"1502F STD *ACT PATTERN	VA0749
STD	VALVE, 2"-2 1/16 5M x 2"1502F STD	VA0699
STD	VALVE, 2"-2 1/16 5M x 2"602F STD	VA0658
STD	VALVE, 2.5" x 2 9/16 10M STD	VA0049
STD	VALVE, 2.5" x 2 9/16 15M STD (ACTUATED)	VA0719
STD	VALVE, 2.5" x 2 9/16 15M STD (GEAR OP)	VA0677
STD	VALVE, 2.5" x 2 9/16 15M STD (MANUAL)	VA0048
STD	VALVE, 2.5" x 2 9/16 15M STD (MANUAL)(HI-TEMP/CO2)	VA0457
STD	VALVE, 2.5" x 2 9/16 15M STD 20"OAL (LOW-T)(ACT PATT)	VA0501
STD	VALVE, 2.5" x 2 9/16 15M STD 20"OAL (LOW-T)(ACT PATT)	VA0500
STD	VALVE, 2.5" x 2 9/16 15M STD 20"OAL (LOW-T)(ACT)	VA0498
STD	VALVE, 2.5" x 2 9/16 15M STD 20"OAL (LOW-T)(GEAR OP)	VA0499
STD	VALVE, 2.5" x 2 9/16 20M STD (LESS ACTUATOR)	VA0410
STD	VALVE, 2.5" x 2 9/16 20M STUD X FLG STD *ACT	VA0773
STD	VALVE, 2.5" x 3"1502 STD 15M (GEAR OP)	VA0045
STD	VALVE, 2.5" x 3"1502 STD 15M (MANUAL)	VA0045M
STD	VALVE, 2.5" x 3"1502 STD 15M (MANUAL) *STINGER PATTERN	VA0477
STD	VALVE, 2.5" x 3.5"IF B/P STD 10M	VA0264
STD	VALVE, 2.5"-2 9/16 15M x 3"1502F STD (LOW-T)(GEAR OP)	VA0539
STD	VALVE, 3" x 3 1/16 10M STD (ACTUATED)	VA0338
STD	VALVE, 3" x 3 1/16 10M STD (GEAR OP)	VA0053
STD	VALVE, 3" x 3 1/16 10M STD (MANUAL)	VA0053M
STD	VALVE, 3" x 3 1/16 10M STD (MANUAL) (HI-TEMP/CO2)	VA0486
STD	VALVE, 3" x 3 1/16 10M STD (MANUAL) (HI-TEMP/CO2)	VA0317
STD	VALVE, 3" x 3 1/16 10M STD (MANUAL) (HI-TEMP/CO2)	VA0527
STD	VALVE, 3" x 3 1/16 15M STD (ACTUATED)	VA0527
STD	VALVE, 3" x 3 1/16 15M STD (GEAR OP)	VA0052
STD	VALVE, 3" x 3 1/16 15M STD (MANUAL)	VA0052M
STD	VALVE, 3" x 3 1/16 15M STD (MANUAL) *ACT PATTERN	VA0052M-OA0184
STD	VALVE, 3" x 3 1/16 15M STD (MANUAL) *ACT PATTERN	VA0052M-OA0152
STD	VALVE, 3" x 3 1/16 15M STD (MANUAL) *STINGER PATTERN	VA0465



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

STD	VALVE, 3" x 3 1/16 15M STUDxFLG STD (ACT)	VA0549
STD	VALVE, 3" x 3 1/16 15M STUDxFLG STD *ACT PATTERN	VA0580
STD	VALVE, 3" x 3 1/16 15M STUDxSTUD STD (ACT)	VA0557
STD	VALVE, 3" x 3 1/16 15M STUDxSTUD STD (GEAR OP)	VA0548
STD	VALVE, 3" x 3 1/16 15M STUDxSTUD STD *ACT PATTERN	VA0602
STD	VALVE, 3" x 3 1/8 5M STD	VA0054
STD	VALVE, 3" x 3"1002 STD 10M (GEAR OP)	VA0590
STD	VALVE, 3" x 3"1502 STD 10M (GEAR OP)	VA0056
STD	VALVE, 3" x 3"1502 STD 10M (MANUAL)	VA0056M
STD	VALVE, 3" x 3"1502 STD 15M (ACTUATED) (VITON) DANFOSS	VA0408V
STD	VALVE, 3" x 3"1502 STD 15M (ACTUATED) DANFOSS	VA0408
STD	VALVE, 3" x 3"1502 STD 15M (GEAR OP 180 DEG)	VA0771
STD	VALVE, 3" x 3"1502 STD 15M (GEAR OP)	VA0055
STD	VALVE, 3" x 3"1502 STD 15M (GEAR OP) *INSERT	VA0595
STD	VALVE, 3" x 3"1502 STD 15M (MANUAL)	VA0055M
STD	VALVE, 3" x 3"1502 STD 15M (MANUAL) (VITON)	VA0055MV
STD	VALVE, 3" x 3"1502 STD 15M (MANUAL) *ACT PATTERN	VA0055M-OA0184
STD	VALVE, 3" x 3"1502 STD 15M (MANUAL) (VITON) *ACT PATT	VA0055MV-OA0184
STD	VALVE, 3" x 3"1502 STD 15M (MANUAL) *GEAR OP PATTERN	VA0055M-OA0152
STD	VALVE, 3" x 3"602 STD 6M	VA0253
STD	VALVE, 3" x 3"LPFF STD 10M	VA0051
STD	VALVE, 3" x 3"LPFF STD 6M (SS PLUG)	VA0051S
STD	VALVE, 3" x 4.38"ACME B/B STD 15M (ACTUATOR)	VA0516
STD	VALVE, 3" x 4.38"ACME B/B STD 15M w/ACT PATTERN	VA0483
STD	VALVE, 3" x 4.38"ACME B/P STD 5M	VA0252
STD	VALVE, 3" x WS30 15M STD (ACT) (HI-TEMP/CO2)	VA0546
STD	VALVE, 3" x WS30 15M STD (GEAR-OP) (HI-TEMP/CO2)	VA0545
STD	VALVE, 3" x WS30 15M STD *ACT PATT (HI-TEMP/CO2)	VA0556
STD	VALVE, 3"-3 1/16 15M x 3"1502F STD (GEAR OP)	VA0502
STD	VALVE, 4" x 4 1/16 10M STD (ACTUATED)	VA0050
STD	VALVE, 4" x 4 1/16 10M STD (GEAR OP)	VA0711
STD	VALVE, 4" x 4 1/16 15M STD (ACTUATED)	VA0387
STD	VALVE, 4" x 4 1/16 15M STD (GEAR OP)	VA0519
STD	VALVE, 4" x 4 1/16 15M STD (LESS ACTUATOR)	VA0388
STD	VALVE, 4" x 4 1/16 15M STUDxFLG STD (ACT)	VA0550
STD	VALVE, 4" x 4 1/16 15M STUDxFLG STD *ACT	VA0581
STD	VALVE, 4" x 4 1/16 15M STUDxSTUD STD (ACT)	VA0558
STD	VALVE, 4" x 4 1/16 15M STUDxSTUD STD (GEAR OP)	VA0551
STD	VALVE, 4" x 4"1002 STD 10M (ACTUATED)	VA0679
STD	VALVE, 4" x 4"1002 STD 10M (GEAR OP)	VA0466
STD	VALVE, 4" x 4"1002 STD 10M (MANUAL)	VA0573
STD	VALVE, 4" x 4"1502 STD 15M (ACTUATED)	VA0366
STD	VALVE, 4" x 4"1502 STD 15M (GEAR OP)	VA0518
STD	VALVE, 4" x 4"1502 STD 15M (GEAR OP)	VA0518-S
STD	VALVE, 4" x 4"1502 STD 15M (NO ACTUATION)	VA0482
STD	VALVE, 4" x 4"602 STD 6M (ACTUATED)	VA0703
STD	VALVE, 4" x 4"602 STD 6M (GEAR OP)	VA0484
STD	VALVE, 4" x 4"LPFF STD 5M	VA0058



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

STD	VALVE, 4" x 4.5"IF B/P STD 10M (GEAR OP)	VA0667
STD	VALVE, 4" x 4.5"IF B/P STD 10M (GEAR OP)	VA0668
STD	VALVE, 4" x 6.38"ACME B/B STD 15M	VA0434
STD	VALVE, 4" x 6.38"ACME B/B STD 15M (ACTUATED)	VA0427
STD	VALVE, 4" x 6.38"ACME B/P STD 15M (ACTUATED)	VA0538
STD	VALVE, 4" x 6.38"ACME B/P STD 15M (GEAR OP)	VA0537
STD	VALVE, 5" x 5 1/8 10M FLGxFLG STD *ACT PATTERN	VA0750
STD	VALVE, 5" x 5 1/8 10M FLGxFLG STD *ACT PATTERN *MOD IN	VA0750-S-STINGER
STD	VALVE, 5" x 5 1/8 10M FLGxFLG STD *ACT PATTERN *SPLIT	VA0750-S
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD (ACT)	VA0565
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD (ACT) *MOD SPLIT IN	VA0565-S-STINGER
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD (ACT) *SPLIT INSERT	VA0565-S
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD *ACT PATTERN	VA0567
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD *ACT PATTERN *MOD S	VA0567-S-STINGER
STD	VALVE, 5" x 5 1/8 10M STUDxFLG STD *ACT PATTERN *SPLIT	VA0567-S
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD (ACT)	VA0560
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD (ACT) *MOD SPLIT IN	VA0560-S-STINGER
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD (ACT) *SPLIT INSERT	VA0560-S
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD *ACT PATTERN	VA0570
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD *ACT PATTERN *MODIF	VA0570-S-STINGER
STD	VALVE, 5" x 5 1/8 15M STUDxFLG STD *ACT PATTERN *SPLIT	VA0570-S
STD	VALVE, 5" x 5 1/8 15M STUDxSTUD STD *ACT	VA0571
STD	VALVE, 5" x 5 1/8 15M STUDxSTUD STD *ACT *MOD SPLIT IN	VA0571-S-STINGER
STD	VALVE, 5" x 5 1/8 15M STUDxSTUD STD *ACT *SPLIT INSERT	VA0571-S
STD	VALVE, 5" x 5"1502 STD 15M (ACTUATED)	VA0568
STD	VALVE, 5" x 5"1502 STD 15M (ACTUATED) *MOD SPLIT INSER	VA0568-S-STINGER
STD	VALVE, 5" x 5"1502 STD 15M (ACTUATED) *SPLIT INSERT	VA0568-S
STD	VALVE, 5" x 8" ACME BXB 15M STD (ACT)	VA0561
H2S	VALVE, 1" x 1 13/16 10M H2S	VA0119
H2S	VALVE, 1" x 1 13/16 15M H2S	VA0122
H2S	VALVE, 1" x 1 13/16 15M x 2"1502F H2S 15M	VA0577
H2S	VALVE, 1" x 1 13/16 15M x 2"1502F H2S 15M Co2	VA0592
H2S	VALVE, 1" x 1"1502 H2S 10M	VA0154
H2S	VALVE, 1" x 1.5"1502 H2S 10M	VA0505
H2S	VALVE, 1" x 2 1/16 10M H2S	VA0120
H2S	VALVE, 1" x 2 1/16 10M H2S (ACTUATED)	VA0341
H2S	VALVE, 1" x 2 1/16 10M H2S wACT PATTERN	VA0407
H2S	VALVE, 1" x 2 1/16 15M H2S	VA0121
H2S	VALVE, 1" x 2 1/16 15M H2S (ACTUATED)	VA0513
H2S	VALVE, 1" x 2 1/16 15M H2S *ACT PATTERN	VA0121-OA0159
H2S	VALVE, 1" x 2 1/16 5M H2S	VA0256
H2S	VALVE, 1" x 2 1/16 5M H2S (ACTUATED) BRC012	VA0497
H2S	VALVE, 1" x 2 1/16 5M H2S *ACT	VA0256-OA0159
H2S	VALVE, 1" x 2 1/16 5M H2S *CORROSION RESISTANT	VA0256-CR
H2S	VALVE, 1" x 2"1502 H2S 10M	VA0118
H2S	VALVE, 1" x 2"1502 H2S 10M (ACTUATED)	VA0547
H2S	VALVE, 1" x 2"1502 H2S 10M (AIR ACTUATED)w/LOCKING PIN	VA0528



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

H2S	VALVE, 1" x 2"1502 H2S 10M *ACT PATT	VA0529
H2S	VALVE, 1" x 2"1502 H2S 10M *STANDARD INSERTS	VA0669
H2S	VALVE, 1" x 2"2202 H2S 15M	VA0099
H2S	VALVE, 1" x 2"2202 H2S 15M (ACTUATED)	VA0540
H2S	VALVE, 1" x 2"602 H2S 6M	VA0747
H2S	VALVE, 1" x 2"LPMM H2S 5M	VA0111
H2S	VALVE, 1" x B20 H2S 15M	VA0294
H2S	VALVE, 1"-2 1/16 10M x 2"1502F H2S	VA0303
H2S	VALVE, 1"-2 1/16 15M x 2"1502F H2S	VA0340
H2S	VALVE, 1"-2 1/16 5M x 1"1502F H2S	VA0775
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S	VA0280
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S (ACTUATED) BRC002	VA0437
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S (ACTUATED) BRC012	VA0727
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S (ACTUATED) SMALL PAT	VA0403
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S *ACT PATT	VA0531
H2S	VALVE, 1"-2 1/16 5M x 2"1502F H2S w1/2"NPT (ACTUATED)	VA0464
H2S	VALVE, 1"-2 1/16 5M x 2"602F H2S	VA0394
H2S	VALVE, 1.3" x 2"2202 H2S 15M	VA0093
H2S	VALVE, 1.3" x 2"2202 H2S 15M (ACTUATED)	VA0426
H2S	VALVE, 1.75" x 1 13/16 15M H2S	VA0132
H2S	VALVE, 1.75" x 1 13/16 15M H2S (ACTUATED)	VA0681
H2S	VALVE, 1.75" x 1 13/16 15M H2S (GEAR OP)	VA0692
H2S	VALVE, 1.75" x 2 1/16 15M H2S	VA0103
H2S	VALVE, 1.75" x 2 1/16 15M H2S (ACTUATED) BRC022	VA0491
H2S	VALVE, 1.75" x 2 1/16 15M H2S (ACTUATED)BRC012	VA0417
H2S	VALVE, 1.75" x 2 1/16 15M H2S *ACT PATTERN BRC012	VA0526
H2S	VALVE, 1.75" x 2 1/16 15M H2S *ACT PATTERN ELOMATIC	VA0103-OA0162
H2S	VALVE, 1.75" x 2"1502 H2S 10M	VA0131
H2S	VALVE, 2" x 2 1/16 10M H2S	VA0134
H2S	VALVE, 2" x 2 1/16 10M H2S (ACTUATED)	VA0326
H2S	VALVE, 2" x 2 1/16 10M H2S (GEAR OP)	VA0738
H2S	VALVE, 2" x 2 1/16 10M H2S *ACT PATTERN	VA0525
H2S	VALVE, 2" x 2 1/16 15M H2S	VA0133-S
H2S	VALVE, 2" x 2 1/16 15M H2S	VA0133
H2S	VALVE, 2" x 2 1/16 15M H2S (ACTUATED FAIL-SAFE)	VA0574
H2S	VALVE, 2" x 2 1/16 15M H2S (ACTUATED)	VA0441
H2S	VALVE, 2" x 2 1/16 15M H2S *ACT PATTERN	VA0133-OA0113
H2S	VALVE, 2" x 2 1/16 5M H2S	VA0018
H2S	VALVE, 2" x 2 1/16 5M H2S (HI-TEMP/CO2)	VA0488
H2S	VALVE, 2" x 2"1502 H2S 10M	VA0109
H2S	VALVE, 2" x 2"1502 H2S 10M (LOW TEMP)	VA0109L
H2S	VALVE, 2" x 2"1502 H2S 10M *ACT PATTERN	VA0109-OA0162
H2S	VALVE, 2" x 2"LPFF H2S 5M	VA0112
H2S	VALVE, 2" x 3"1502 H2S 10M (GEAR OP)	VA0741
H2S	VALVE, 2" x B20 H2S 15M	VA0010
H2S	VALVE, 2" x WS20TN H2S 15M (HI-TEMP)	VA0354
H2S	VALVE, 2" x WS20TN H2S 15M (HI-TEMP) (ACTUATED)	VA0413
H2S	VALVE, 2" x WS20TN H2S 15M (HI-TEMP) (AIR ACTUATED)	VA0414



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

H2S	VALVE, 2" x WS20TN H2S 15M (HI-TEMP) *ACT	VA0354-OA0162
H2S	VALVE, 2"-2 1/16 10M x 2"1502F H2S	VA0533
H2S	VALVE, 2"-2 1/16 10M x 2"1502F H2S (ACTUATED)	VA0336
H2S	VALVE, 2"-2 1/16 10M x 2"1502F H2S *ACT PATT	VA0541
H2S	VALVE, 2"-2 1/16 10M x 2"1502F H2S *LOW TEMP	VA0503
H2S	VALVE, 2"-2 1/16 15M x 2"1502F H2S	VA0440
H2S	VALVE, 2"-2 1/16 15M x 2"1502F H2S (ACTUATED)	VA0517
H2S	VALVE, 2"-2 1/16 5M x 2"1502F H2S	VA0435
H2S	VALVE, 2"-2 1/16 5M x 2"1502F H2S (ACTUATED)	VA0492
H2S	VALVE, 2.5" x 2 9/16 15M H2S	VA0298
H2S	VALVE, 2.5" x 3"1502 H2S 10M (GEAR OP)	VA0211
H2S	VALVE, 2.5" x 3"1502 H2S 10M (MANUAL)	VA0211M
H2S	VALVE, 2.5" x 3.5"IF B/P H2S 10M	VA0138
H2S	VALVE, 2.5" x 4.12"ACME B/P H2S 10M	VA0261
H2S	VALVE, 2.5" x 4.12"ACME P/P H2S 10M	VA0260
H2S	VALVE, 3" x 3 1/16 10M H2S (GEAR OP)	VA0108
H2S	VALVE, 3" x 3 1/16 10M H2S (MANUAL)	VA0108M
H2S	VALVE, 3" x 3 1/16 10M H2S (MANUAL) (HI-TEMP/CO2)	VA0402
H2S	VALVE, 3" x 3 1/16 15M H2S (GEAR OP)	VA0598
H2S	VALVE, 3" x 3 1/8 5M H2S (MANUAL)	VA0104
H2S	VALVE, 3" x 3"1502 H2S 10M (GEAR OP)	VA0016
H2S	VALVE, 3" x 3"1502 H2S 10M (MANUAL)	VA0016M
H2S	VALVE, 3" x 3"2202 H2S 15M (GEAR OP)	VA0242
H2S	VALVE, 3" x 3"602 H2S 6M	VA0228
H2S	VALVE, 3" x WS30 15M H2S (GEAR-OP)	VA0743
H2S	VALVE, 4" x 4 1/16 10M H2S (ACTUATED)	VA0522
H2S	VALVE, 4" x 4"1502 H2S 10M (GEAR OP)	VA0520
H2S	VALVE, 4" x 4"602 H2S 6M (ACTUATED)	VA0763



MSI-Manifold Systems Ironworks SA
 Avenue Choiseul 19A – 1290 Versoix – Switzerland
 Ph: +41 22 774 29 61 – Fax: +41 22 774 29 63
 Email : sales@msi-sa.biz – Web : www.msi-sa.biz

Plug Valves, SPM/FMC Top Entry style

Service	Part Description	Part Number
STD	VALVE-TE, .38" x 2"1502 STD 15M	VA0698
STD	VALVE-TE, 1" x 1"1502 STD 15M	VA0639
STD	VALVE-TE, 1" x 1.5"1502 STD 15M	VA0640
STD	VALVE-TE, 1" x 2 1/16 STD 15M	VA0645
STD	VALVE-TE, 1" x 2"1502 STD 15M	VA0582
STD	VALVE-TE, 1" x 2"1502 STD 15M (ACTUATED)	VA0690
STD	VALVE-TE, 1" x 2"1502 STD 15M *ACT PATTERN	VA0700
STD	VALVE-TE, 1" x 2"602 STD 6M	VA0709
STD	VALVE-TE, 1" x 2"LPMM STD 10M	VA0583
STD	VALVE-TE, 2" x 2 1/16 10M STD	VA0767
STD	VALVE-TE, 2" x 2 1/16 10M STD (ACTUATED)	VA0768
STD	VALVE-TE, 2" x 2 1/16 15M STD	VA0603
STD	VALVE-TE, 2" x 2"1502 STD 15M	VA0588
STD	VALVE-TE, 2" x 2"1502 STD 15M (ACTUATED)	VA0680
STD	VALVE-TE, 2" x 2"1502 STD 15M *ACT PATTERN	VA0701
STD	VALVE-TE, 2" x 2"1502 STD 15M *ACT PATTERN (SPM)	VA0588-OA0338
STD	VALVE-TE, 2" x 2"1502 STD 15M *ACT PATTERN (SPM)	VA0697
STD	VALVE-TE, 2" x 2"602 STD 6M	VA0762
STD	VALVE-TE, 2" x 2"LPFF STD 10M	VA0589
STD	VALVE-TE, 2" x WS20TN STD 15M (HI-TEMP)	VA0604
STD	VALVE-TE, 2" x WS20TN STD 15M (HI-TEMP) GREASEAL	VA0713
STD	VALVE-TE, 3" x 3"1502 STD 15M (GEAR OP)	VA0657
STD	VALVE-TE, 3" x 3"1502 STD 15M (MANUAL)	VA0664
H2S	VALVE-TE, 1" x 2"1502 H2S 10M	VA0606
H2S	VALVE-TE, 1" x 2"LPMM H2S 5M	VA0607
H2S	VALVE-TE, 2" x 2"1502 H2S 10M	VA0608
H2S	VALVE-TE, 2" x 2"LPFF H2S 5M	VA0609